

CAPLOCK™ ACTION CAMERA HELMET MOUNT



PGYTECH

In The Box



User
Guide x1



CapLock™
Action Camera
Helmet Mount x 1



Action Camera
Adapter x1



Thumb
Screw x1



1/4"
Adapter x1



S4 L-shape
Wrench x1



Curved Mount
Base x 2



Flat Mount
Base x 2



VHB Tape for
Mount Base x 2



Safety
Base x 2



VHB Tape for
Safety Base x 1



Safety
lanyard x 1

Specifications


Product Name:

PGYTECH CapLock™ Action Camera Helmet Mount

Item Number: P-GM-225

Main Materials: Aluminium, PC+ABS, Silica gel


Assembly



1 2 Tear sticker.




3 Tie safety lanyard.




4 5 Please fix the two mount bases according to the length of the lanyard.

Note: When temperature is $\geq 10^{\circ}\text{C}$, press and adhere the base, then wait at least 24 hours before installing the mount; When temperature is $< 10^{\circ}\text{C}$, heat the base tape with a hairdryer, then press and adhere the base, and wait at least 24 hours before installing the mount.



9 Please push the mount till the end in case the gear falls off.




10 Please attach the safety lanyard to the product in case the gear falls off.


Install Adapter




Disassembly



① Untie the safety lanyard.




② To detach the adhesive mount, press the buckle on both sides and simultaneously push backwards.




Note: you can remove the adhesive mount and leave the base on the helmet, which is convenient for future mounts.

Remove Adapter



Functions



Note: The two balls allow tilt movement and 360° rotation.



The unlock button
(Press the button
to unlock and
take out the plate)



CapLock™
action camera
quick release
interface



WARNING

1. Note: When temperature is $\geq 10^{\circ}\text{C}$, press and adhere the base, then wait at least 24 hours before installing the mount; When temperature is $< 10^{\circ}\text{C}$, heat the base tape with a hairdryer, then press and adhere the base, and wait at least 24 hours before installing the mount.
2. The weight capacity is 300g.
3. Recommended ambient temperature: $-10^{\circ}\text{C} \sim 40^{\circ}\text{C}$.

**ARE YOU READY TO CREATE WITH PGYTECH?
WIN THE WEEKLY CHALLENGE AND
GET YOUR FREEBIES.**



#CREATEWITHPGYTECH #PGYTECH



pgytech.com



[pgytechglobal](#)



[PGYTECH](#)



[PGYTECH](#)



[PGYTECH](#)



Question & Support: support@pgytech.com